

Data Sheet

VIAVI 4100 Series OTDR A, B and C Modules

For T-BERD/MTS-2000, –4000 V2, –5800, CellAdvisor 5G, OneAdvisor 800 and FTH-9000

VIAVI Solutions 4100-Series OTDR modules let field technicians rapidly, reliably, and cost-effectively install, turn up, and troubleshoot any optical network architecture: data center interconnection, metro, long-haul and FTTx/access for wireless/5G x-haul, point-to-point or point-to-multipoint passive optical networks (PONs).

Fiber infrastructure is the foundation of the network performance and the quality of delivered services. An OTDR is the only tool that verifies the condition of installed cables and passive components to ensure fiber links meet design specifications and contractor's workmanship meets the required quality.

Module portability allows migration of fiber test capabilities between different VIAVI platforms, offering the flexibility to move existing fiber certification tools to different technologies such as coax and RF, active xWDM, MPO/ribbon cables or network layer tests such as Ethernet, BERT, CPRI, etc.



T-BERD/MTS-4000 V2 Two-slot handheld modular platform for testing fiber networks



T-BERD/MTS-2000 One-slot handheld modular platform for testing fiber networks



T-BERD/MTS-5800 Handheld test instrument for testing 10 G Ethernet and fiber networks



OneAdvisor 800 All-in-One wireline and wireless network Installation and Maintenance Test Solution

Key Features

- Up to 46 dB dynamic range and 256,000 acquisition points
- PON-optimized for next generation architectures, up to 1x256 split ratio and unbalanced and indexed splitters
- Dual/tri-wavelength versions with 1310/1550/1625 or 1650 nm
- Single test port connection for standard and filtered wavelengths faster, error free testing avoiding customer services disruption
- Instant bi-directional OTDR event loss analysis "TrueBIDIR" (patented)
- Consolidated reporting for all wavelengths tested reduces volume of test results to manage by 50%
- Test port condition check to prevent poor launch conditions and inaccurate event detection
- Supports SLM application tailored for various network applications (FTTA, FTTH, Enterprise, High fiber count cables)
- Field upgradeable for FiberComplete PRO applications – OTDR loopback, bi-directional OTDR analysis (TrueBIDIR), high fiber count (MPO)



Standard feature benefits include:

- Standard multi-pulses acquisition (**SmartAcq**) improves event detection (splices, connectors, bends, ...) and removes the need for expensive and heavy launch cables.
- Icon-based map view (**Smart Link Mapper** SLM) eliminates OTDR interpretation errors and speeds up the results analysis with instant identification of faults and impairments
- The **SmartTEST** mode assists the fiber technicians (new or experienced) throughout the steps of OTDR testing. It is eliminating the complex OTDR tasks (setup configuration, analysis and reporting) and guiding the user through an easy and clear test process.
- For more information, please refer to the OTDR Features brochure.

Specifications (Typical at 25°C)

Optical interfaces FC, SC and LC Technical characteristics Iaser safety class (21CFR) Class 1 Group index range 1.30000 to 1.70000 in 0.00001 steps Sampling points Up to 256,000 Pulse width From 3 ns//s ns to 20 µs Distance measurement Modes Automatic or dual cursor Display range 0.1 up to 400 km Cursor resolution 1 cm Sampling resolution 4 cm Accuracy ² ±(0.5 m + sampling resolution + 0.001% x distance) Attenuation measurement Modes Automatic, manual, 2-point, 5-point, and LSA Display resolution 0.001 dB Linearity ±0.03 dB/dB Reflectance/ORL measurement Reflectance accuracy ±2 dB Display resolution 0.01 dB Threshold -11 to -99 dB in 1 dB steps Optical light source (standard) Wavelengths Same as OTDR port ³ Output power level -3.5 dBm in CW mode Tone generation 270Hz, 330Hz, 1 KHz, 2 KHz Auto A mode Yes (with VIAVI power meters) </th <th>General</th> <th></th>	General				
Interchangeable optical connectorsFC, SC and LCTechnical characteristicsLaser safety class (2TCFR)Class 1Group index range1.30000 to 1.70000 in 0.00001 stepsSampling pointsUp to 256,000Pulse widthFrom 3 ns/5 ns to 20 µsDistance measurementModesAutomatic or dual cursorDislay range0.1 up to 400 kmCursor resolution1 cmSampling resolution4 cmAccuracy ² ± (0.5 m + sampling resolution +0.001% x distance)Attenuation measurementModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity± 0.03 dB/dBReflectance/ORL measurementReflectance accuracy± 2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)270Hz, 330Hz, 1 Hz, 2kHzAuto A modeYes (with VIAVI power meters)Stability (8h)<± 0.13 dB	Weight	0.35 kg (0.77 lb)			
Technical characteristicsLaser safety class (21CFR)Class 1Group index range1.30000 to 1.70000 in 0.00001 stepsSampling pointsUp to 256,000Pulse widthFrom 3 ns//s ns to 20 µsDistance measurementModesAutomatic or dual cursorDisplay range0.1 up to 400 kmCursor resolution1 cmSampling resolution4 cmAccuracy2±(0.5 m + sampling resolution ±0.001% x distance)Attenuation measurement0.001 dBModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port3Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2 kHzAuto \armodeYes (with VIAVI power meters)Stability (8h)<±0.1dB	Optical interfaces				
Laser safety class (21CFR)Class 1Group index range1.30000 to 1.70000 in 0.00001 stepsSampling pointsUp to 256,000Pulse widthFrom 3 ns1/5 ns to 20 µsDistance measurementModesAutomatic or dual cursorDisplay range0.11 up to 400 kmCursor resolution1 cmSampling resolution4 cmAccuracy2±(0.5 m + sampling resolution +0.001% x distance)Attenuation measurement0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurement0.001 dBBisplay resolution0.01 dBLinearity±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)270Hz, 330Hz, 1 kHz, 2kHzWavelengthsSame as OTDR port ¹ Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto A modeYes (with VIAVI power meters)Stability (8h)<±0.155 dBm	Interchangeable optical connectors	FC, SC and LC			
Group index range130000 to 1.70000 in 0.00001 stepsSampling pointsUp to 256,000Pulse widthFrom 3 ns//5 ns to 20 µsDistance measurementModesAutomatic or dual cursorDisplay range0.1 up to 400 kmCursor resolution1 cmSampling resolution4 cmAccuracy2±(0.5 m + sampling resolution +0.001% x distance)Attenuation measurementModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port3Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto A modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Technical characteristics				
Sampling pointsUp to 256,000Pulse widthFrom 3 ns1/5 ns to 20 µsDistance measurementFrom 3 ns1/5 ns to 20 µsModesAutomatic or dual cursorDisplay range01 up to 400 kmCursor resolution1 cmSampling resolution4 cmAccuracy2±(0.5 m + sampling resolution +0.001% x distance)Attenuation measurementModesModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port3Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto A modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Laser safety class (21CFR)	Class 1			
Pulse widthFrom 3 nst/5 ns to 20 μsDistance measurementModesAutomatic or dual cursorDisplay range01 up to 400 kmCursor resolution1 cmSampling resolution4 cmAccuracy²± (0.5 m + sampling resolution +0.001% x distance)Attenuation measurementModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity± 0.03 dB/dBReflectance/ORL measurementReflectance accuracy± 2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port³Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto \u00exYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Group index range	1.30000 to 1.70000 in 0.00001 steps			
Distance measurementModesAutomatic or dual cursorDisplay range0.1 up to 400 kmCursor resolution1 cmSampling resolution4 cmAccuracy²±(0.5 m + sampling resolution +0.001% x distance)Attenuation measurementModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port³Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Sampling points	Up to 256,000			
ModesAutomatic or dual cursorDisplay range0.1 up to 400 kmCursor resolution1 cmSampling resolution4 cmAccuracy2±(0.5 m + sampling resolution +0.001% x distance)Attenuation measurementModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port3Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Pulse width	From 3 ns ¹ /5 ns to 20 µs			
Display range01 up to 400 kmCursor resolution1 cmSampling resolution4 cmAccuracy2±(0.5 m + sampling resolution +0.001% x distance)Attenuation measurementModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port3Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Distance measurement				
Cursor resolution1 cmSampling resolution4 cmAccuracy2±(0.5 m + sampling resolution +0.00% x distance)Attenuation measurement	Modes	Automatic or dual cursor			
Sampling resolution4 cmAccuracy2±(0.5 m + sampling resolution +0.001% x distance)Attenuation measurementModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port3Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto \u00e1 modeYes (with VIAVI power meters)Stability (8h)<±0.1dB	Display range	0.1 up to 400 km			
Accuracy2±(0.5 m + sampling resolution +0.001% x distance)Attenuation measurementModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port3Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Cursor resolution	1 cm			
Attenuation measurementModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port ³ Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Sampling resolution	4 cm			
ModesAutomatic, manual, 2-point, 5-point, and LSADisplay resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port³Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Accuracy ²	±(0.5 m + sampling resolution +0.001% x distance)			
Display resolution0.001 dBLinearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port³Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Attenuation measurement				
Linearity±0.03 dB/dBReflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port³Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto \n modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Modes	Automatic, manual, 2-point, 5-point, and LSA			
Reflectance/ORL measurementReflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port³Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Display resolution	0.001 dB			
Reflectance accuracy±2 dBDisplay resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port³Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Linearity	±0.03 dB/dB			
Display resolution0.01 dBThreshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port³Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Reflectance/ORL measurement				
Threshold-11 to -99 dB in 1 dB stepsOptical light source (standard)WavelengthsSame as OTDR port³Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Reflectance accuracy	±2 dB			
Optical light source (standard)WavelengthsSame as OTDR port3Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Display resolution	0.01 dB			
WavelengthsSame as OTDR port³Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Threshold	-11 to -99 dB in 1 dB steps			
Output power level-3.5 dBm in CW modeTone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Optical light source (standard)				
Tone generation270Hz, 330Hz, 1 kHz, 2kHzAuto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Wavelengths	Same as OTDR port ³			
Auto λ modeYes (with VIAVI power meters)Stability (8h)<±0.1 dB	Output power level	-3.5 dBm in CW mode			
Stability (8h)<±0.1 dBPower meter (optional)-3 to -55 dBmInput power range-3 to -55 dBmCalibrated wavelengths1310/1490/1550/1625/1650 nm	Tone generation	270Hz, 330Hz, 1 kHz, 2kHz			
Power meter (optional)Input power range-3 to -55 dBmCalibrated wavelengths1310/1490/1550/1625/1650 nm	Auto λ mode	Yes (with VIAVI power meters)			
Input power range-3 to -55 dBmCalibrated wavelengths1310/1490/1550/1625/1650 nm	Stability (8h)	<±0.1 dB			
Calibrated wavelengths 1310/1490/1550/1625/1650 nm	Power meter (optional)				
	Input power range	-3 to -55 dBm			
Power level accuracy ⁴ ±0.5 dB	Calibrated wavelengths	1310/1490/1550/1625/1650 nm			
	Power level accuracy ⁴	±0.5 dB			

2 4100 Series OTDR A, B and C Modules

OTDR specifications (Typical at 25°C)							
	Central wavelengths⁵	RMS dynamic range ⁶	Event dead zone ⁷	Attenuation dead zone ⁸	Splitter attenuation dead zone ⁹		
4100 A	1310±20 nm 1550±20 nm 1625±15 nm	37 dB ¹¹ 36 dB ¹¹ 36 dB ¹¹	0.65 m	2.5 m	_		
4100 B	1310±20 nm 1550±20 nm 1625±10 nm 1650+10/-5 nm	43 dB 41 dB 41 dB 40 dB	0.60 m	2.5 m	45 m ⁹		
4100 C	1310±20 nm 1550±20 nm 1625±10 nm 1650±15 nm	46 dB 45 dB 45 dB 43 dB	0.50 m	2.5 m	20 m ¹⁰		

¹ With 4100 C OTDR modules and EPULSE3NS software

²Excluding group index uncertainties

³Except filtered wavelengths

 $^{4}\mbox{At}$ calibrated wavelengths, at -30 dBm excluding connection uncertainty

 $^{\textrm{s}}\text{Laser}$ at 25°C and measured at 10 μs

⁶The one-way difference between the extrapolated backscattering level at the start of the fiber and the RMS noise level, after 3 minutes averaging

 7 Measured at ±1.5 dB down from the peak of an unsaturated reflective event, using 5ns pulsewidth at 1310 nm

⁸Measured at ±0.5 dB down from the linear regression using a FC/UPC-type reflectance, using 5 ns pulsewidth at 1310 nm

⁹Measured on a 16 dB loss (typical 1x32 split ratio) non-reflective splitter at 1310nm, using 200 ns pulsewidth

¹⁰Measured on a 16 dB loss (typical 1x32 split ratio) non-reflective splitter at 1310nm, using 100 ns pulsewidth

"RMS dynamic range extended to 40/38/38 dB with EXTRANGE or EXTRANGE-UPG license

Ordering Information

Description	Part number			
4100 Module A OTDR – 1310/1500 nm – PC/APC	E4126A-PC/-APC			
4100 Module A OTDR – 1310/1625 nm – PC/APC	E4106A-PC/-APC			
4100 Module A OTDR – 1310/1550/1625 nm – PC/APC	E4136A-PC/-APC			
4100 Module B OTDR – 1310/1550 nm – PC/APC	E4126B-PC/-APC			
4100 Module B OTDR – 1310/1550/1625 nm – PC/APC	E4136B-PC/-APC			
4100 Module B OTDR – 1310/1550/Filtered 1650 nm – APC	E4138FB65-APC			
4100 Module B OTDR – Filtered 1650 nm – APC	E4118FB65-APC			
4100 Module C OTDR – 1310/1550 nm – PC/APC	E4126C-PC/-APC			
4100 Module C OTDR – 1310/1550/1625 nm – PC/APC	E4136C-PC/-APC			
4100 Module C OTDR – 1310/1550/Filtered 1625 nm – APC	E4136FC-APC			
4100 Module C OTDR – 1310/1550/Filtered 1650 nm – APC	E4138FC65-APC			
Universal PC connector adapters	EUSCADS, EULCADS, EUFCADS			
Universal APC connector adapters	EUSCADS-APC, EULCADS-APC, EUFCADS			
Optical power meter option	E410TDRPM			
Add 1550 nm Wavelength to 4100 Module A OTDR	E4115-UPG			
Extend dynamic range to 4100 Module A OTDR	EXTRANGE/EXTRANGE-UPG			
3 ns pulse width option for 4100 Module C OTDR	EPULSE3NS			
TrueBIDIR – Bi-directional OTDR analysis	TRUEBIDIR-FCOMP-PRO			
FiberComplete PRO – Loopback Bi-Directional OTDR Mode	ELOOPBACK-FCOMP-PRO			

Test Process Automation (TPA)

Allows your team to deliver expert-level test results and close projects on the first try, every time. TPA is a closed loop test system that optimizes workflows, eliminates manual, error prone work and automates immediate data reporting for job close out, team progress updates and network health analytics. Execute jobs efficiently to ensure high quality network builds, rapid turn-up/activation and enhanced operational visibility.

Inspect Before You Connect (IBYC)

Contamination is the number 1 reason for troubleshooting optical networks. Proactive inspection and cleaning of fiber connectors can prevent poor signal performance, equipment damage, and network downtime.

VIAVI Care Support Plans

Increase your productivity for up to 5 years with optional VIAVI Care Support Plans:


- Maximize your time with on-demand training, priority technical application support and rapid service.
- Maintain your equipment for peak performance at a low, predictable cost.

Plan availability depends on product and region. Not all plans are available for each product or in every region. To find out which VIAVI Care Support Plan options are available for this product in your region, contact your local representative or visit: viavisolutions.com/viavicareplan

									"5-year plans only
Plan	Objective	Technical Assistance	Factory Repair	Priority Service	Self-paced Training	5 Year Battery and Bag Coverage	Factory Calibration	Accessory Coverage	Express Loaner
BronzeCare	Technician Efficiency	Premium	\checkmark	\checkmark	\checkmark				
SilverCare	Maintenance & Measurement Accuracy	Premium	\checkmark	\checkmark	\checkmark	\checkmark^{\star}	\checkmark		
MaxCare	High Availability	Premium	\checkmark	\checkmark	\checkmark	\checkmark^{\star}	\checkmark	\checkmark	\checkmark



Features



To reach the VIAVI office nearest you. visit viavisolutions.com/contact

© 2023 VIAVI Solutions Inc. Product specifications and descriptions in this document are subject to change without notice. Patented as described at viavisolutions.com/patents 4100abc-otdrmodule-ds-fop-nse-ae 30192912 908 0823

*E year plans only



